PCT

WORLD INTELLECTUAL PROPERTY ORGANIZATION International Bureau



INTERNATIONAL APPLICATION PUBLISHED UNDER THE PATENT COOPERATION TREATY (PCT)

			(/
(51) International Patent Classification 5:		(11) International Publication Number:	WO 93/03649
A46B 11/00	A1	(43) International Publication Date:	4 March 1993 (04.03.93)
		· · · · · · · · · · · · · · · · · · ·	

(21) International Application Number:	PCT/US92/06770	(72) I
--	----------------	--------

(22) International Filing Date: 13 August 1992 (13.08.92)

(30) Priority data:
749,137
23 August 1991 (23.08.91)
US

898,471 15 June 1992 (15.06.92) US

(60) Parent Applications or Grants

(63) Related by Continuation
US
Filed on
US
15 June 1992 (15.06.92)
US
749,137 (CON)

(71) Applicant (for all designated States except US): GILLETTE CANADA INC. [CA/CA]; 16700 Trans Canada, Kirkland, Quebec H9H 4Y8 (CA).

(72) Inventors; and

(75) Inventors/Applicants (for US only): TSENG, Mingchih, M. [US/US]; 4 Partridge Drive, Hingham, MA 02043 (US). PHILBROOK, Carl, M. [US/US]; 48 Jamaica St. #1, Jamaica Plain, MA 02130 (US).

(74) Agents: HANDELMAN, Joseph, H. et al.; Ladas & Parry, 26 West 61 Street, New York, NY 10023 (US).

(81) Designated States: AT, AU, BB, BG, BR, CA, CH, CS, DE, DK, ES, FI, GB, HU, JP, KP, KR, LK, LU, MG, MN, MW, NL, NO, PL, RO, RU, SD, SE, US, European patent (AT, BE, CH, DE, DK, ES, FR, GB, GR, IE, IT, LU, MC, NL, SE), OAPI patent (BF, BJ, CF, CG, CI, CM, GA, GN, ML, MR, SN, TD, TG).

Published

With international search report. Before the expiration of the time limit for amending the claims and to be republished in the event of the receipt of amendments.

(54) Title: SUSTAINED-RELEASE MARTRICES FOR DENTAL APPLICATION

23 August 1991 (23.08.91)

(57) Abstract

Filed on

A sustained-release matrix (20) for dental application includes either an anti-microbial agent or a colorant that is released from the matrix (20) when the matrix (20) contacts water. The preferred matrices (20) include a water-soluble polymer and a water-insoluble support resin.

FOR THE PURPOSES OF INFORMATION ONLY

Codes used to identify States party to the PCT on the front pages of pamphlets publishing international applications under the PCT.

АT	Austria	FI	Finland	MN	Mongolia
ΑU	Australia	FR	France	MR	Mauritania
BB	Barbados	GA	Gabon	MW	Malawi
BE	Belgium	GB	United Kingdom	NL	Netherlands
BF	Burkina Faso	GN	Guinea	NO	Norway
BG	Bulgaria	GR	Greece	NZ	New Zealand
BJ	Benin	HU	Hungary	PL	Poland
BR	Brazil	ΙE	Ireland	PT	Portugal
CA	Canada	ŧΤ	Italy	RO	Romania
CF	Central African Republic	JP	Japan	RU	Russian Federation
CG	Congo	KP	Democratic People's Republic	SD	Sudan
CH	Switzerland		of Korca	SE	Sweden
CI	Côte d'Ivoire	KR	Republic of Korea	SK	Slovak Republic
CM	Cameroon	LI	Liechtenstein	SN	Senegal
CS	Czechoslovakia	LK	Sri Lanka	SU	Soviet Union
CZ	Czech Republic	LU	Laxembourg	TD	Chad
DE	Germany	MC	Monaco	TG	Togo
DK	Denmark	MG	Madagascar	UA	Ukraine
ES	Spain	MI	Mali	US	United States of America

きり続

SUSTAINED-RELEASE MATRICES FOR DENTAL APPLICATION

The invention relates to sustained-release matrices.

Most humans suffer from tooth decay

and/or periodontal disease caused by bacteria in
the mouth. As a result, decreasing the number of
bacteria in the mouth has long been the target of
persons working in the health care field. The most
common way of minimizing the number of bacteria is
to brush and floss the teeth regularly, and to
visit a dental hygienist to have the teeth and gums
cleaned thoroughly. Another prior approach is oral
rinsing, including with a solution containing a
known anti-microbial agent like chlorhexidine
digluconate.

are a large number of bacteria clinging to the bristles, even after the brush has been rinsed.

This, of course, is undesirable, and these bacteria typically will multiply on the bristles between uses. To counter this problem, self-sterilizing toothbrushes have been described in the prior art. One such self-sterilizing toothbrush is described by White et al., U.S. Patent No. 2,216,333, and includes a combination of a water soluble salt (e.g., sodium carbonate) with an anti-microbial agent (e.g., sulfur). The two are fused to a solid hard body and attached to the head of the toothbrush at the base of the bristles. When

- 2 -

exposed to water the sodium carbonate dissolves, forming an alkaline solution that in turn dissolves some sulfur, which kills bacteria.

Toothbrushes wear out with extended use.

5 Breuer et al., U.S. Pat. No. 4,802,255, describe a toothbrush that includes filaments that release a dye, and thus change color, in response to increased use of the filament. The change in color provides a means for monitoring the degree of wear of the toothbrush.

Kent, U.S. Pat. No. 5,061,106, describes including capsules or microspheres in the tuft holes in which the bristles of a toothbrush are mounted. The capsules or microspheres include a disinfectant or medicant that is released during use. A dye may also be included in the structures. The dye also is released over time to enable the user to become aware of when the contents of the capsules are depleted.

matrices that are particularly suited for use with toothbrushes. The matrices can include an antimicrobial agent that is released over time when the matrices are exposed to water. The matrices may also include a colorant and a water-leachable substance that is released over time when the matrices are exposed to water to cause the matrix to change color.

In one aspect the invention features an oral brush that includes a sustained-release matrix made from a support resin, a water-soluble substance (preferably a water-soluble polymer), and an anti-microbial agent. When the matrix contacts water, the water-soluble substance dissolves, causing the release of the anti-microbial agent.

An oral brush, as used herein, is any brush that includes a handle and a head attached to

a brush designed for insertion into the mouth. The brush portion preferably is made from the common bristles found in toothbrushes, but can also be designed for massaging the gums rather than the teeth. For example, Kaminski et al., USSN 07/724,129, which was filed on July 1, 1991, is assigned to the same assignee as the present application and is hereby incorporated by reference, describes an interdental foam brush in which the brush portion is made of a soft polyurethane foam.

A support resin, as used herein, is an essentially water-insoluble polymer that provides structural integrity to the matrix as the other components of the matrix -- the water-soluble polymer and anti-microbial agent -- dissolve or leach out. A further description of what constitutes a support resin is included in the Other Embodiments section. Preferably, the polymer used as the support resin should have a low processing temperature (less than 130°C.) so that it can be readily combined with anti-microbial agents that are unstable at high temperature. Also, the polymer should not become brittle as the other components dissolve or leach out, so that the matrix does not break apart readily when handled.

Preferred polymers for the support resin include polystyrene, polyurethane ethylene vinyl acetate, polyethylene, styrene/rubber, and ethylene/propylene. The more preferred support resin is an ethylene vinyl acetate polymer. Most preferably the ethylene vinyl acetate polymer includes between 5% and 50% vinyl acetate, and has a softening point of between 100°C. and 35°C., respectively.

A water-soluble substance, as used herein, is a substance that is sufficiently soluble

- 4 -

in water that it will dissolve out of the matrix during contact with water to form channels in the matrix through which the anti-microbial agent will leach into the water. A further description of what constitutes a water-soluble substance is provided in the Other Embodiments section.

The preferred water-soluble substances are polymers. The preferred polymers are starches, polyvinyl alcohols, polyethylene oxides,

10 hydroxyalkyl starches, hydroxyethyl and hydroxypropyl celluloses, and gelatins. The most preferred are polyethylene oxides, most preferably a Polyox having a molecular weight of between 100,000 and 5,000,000.

that kills bacteria. The preferred anti-microbial agent for use in the matrix is chlorhexidine, most preferably the digluconate salt thereof; the hydrochloride and diacetate salts of chlorhexidine can also be used. Other anti-microbial agents that can be included in the matrix include tetracycline (and other antibiotics), and domiphen bromide.

Preferably, the matrix is a flat template having a thickness of up to 4 mm and is attached to the head of the body at the base of the bristles. The preferred templates have a surface area of at least 0.01 in², more preferably at least about 0.1 in². Most preferably, the template has the same surface area as the toothbrush head (minus the bristles). In this position the template is exposed to water when the brush is rinsed and to saliva when it is inserted into the mouth, and can supply the anti-microbial agent to the bristles for self-sterilization and to the mouth to kill bacteria. The matrix can also be attached to any other part of the brush (e.g., the back of the

brush head or at the junction of the brush head and

handle), provided that the part of the brush it is attached to is sufficiently close to the head end that it typically is inserted into the mouth during use.

5 In other preferred embodiments, the matrix includes two layers, joined together. By "two layers", it is meant that one section of the template has a different composition than a second section. The first outer layer includes a support 10 resin or a water-soluble polymer, and an antimicrobial agent; the second inner layer includes the support resin. Significantly, the first layer can include a large quantity of anti-microbial agent because the layer includes less (or none) of 15 the support resin, yet the layer is stable because the co-extruded second layer provides the necessary support. The second layer may also include, optionally, some water-soluble polymer and/or antimicrobial agent.

The invention features, in another aspect, an oral brush that includes a template including a water-soluble polymer and an antimicrobial agent.

aspect, a matrix including ethylene vinyl acetate, polyethylene oxide, and an anti-microbial agent such as chlorhexidine. The matrix can be sized, shaped, and otherwise designed for short or long term placement at some point in the mouth. The matrix can also be designed as a template for inclusion on a toothbrush, or can be used to coat dental floss, or other dental instrument(s).

The matrices of the invention provide a controlled release of an anti-microbial agent into the mouth. When included on a toothbrush, the matrix repeatedly supplies controlled dosages of the agent to kill bacteria in the mouth and on the

- 6 -

bristles of the brush. The matrices are easy to manufacture, and their composition, shape and thickness can be adjusted to provide the best properties for the intended use. For example, the amount and type of polyethylene oxide in the preferred embodiment can be modified so that the viscosity of the released polymer in solution is less than the viscosity of the saliva in the mouth.

Another aspect of the invention features 10 a wear-indicator oral brush that includes a matrix containing a colorant (e.g., a dye) and a waterleachable substance that is released from the matrix when the oral brush is used to cause the matrix to change color after repeated (at least 5) 15 typical uses. The preferred matrix is a template that includes two co-extruded or co-molded layers. The outer layer, which contacts water and saliva during brushing, preferably includes the waterleachable substance, which can be, for example, a 20 water-soluble polymer like polyethylene oxide, or the colorant itself, or a combination of the two. The second, inner, layer preferably includes a support resin, and can also include a colorant (e.g., TiO₂) that provides the template with a 25 different color, or shade of color, than the colorant included in the outer layer. The first layer preferably also includes a support resin, although less than the amount included in the second layer, and also can include an anti-30 microbial agent.

The oral brushes having a matrix including a colorant, i.e., pigment or dye, provide a means to monitor the degree of wear of the brush. Where the water-leachable substance includes the colorant, over time as the brush is used the colorant is released, causing the matrix to change color. In those embodiments in which the colorant

- 7 -

is not water-leachable and thus is not released from the matrix, typically the portion of the template including a water-leachable substance dissolves away through repeated use of the brush to expose the section of the matrix that includes the colorant, providing an indication of wear. The amounts and types of colorant in the matrix can be adjusted so that the color of the matrix changes after the number of uses through which a typical brush should be used. When the colored matrix also includes an anti-microbial agent, the change of colorant can be designed to correspond with the depletion of the agent in the matrix.

Other features and advantages of the
invention will be apparent from the description of
the preferred embodiment thereof, and from the
claims.

Figure 1 is a perspective view of the preferred toothbrush.

Figures 2a-2e provide perspective views of some alternative two-layer templates. Figure 2f is a cross-sectional view of the template of Figure 2e, taken along line A-A. In these figures the holes through which the bristles would be inserted 25 are not shown.

Referring to Fig. 1 a toothbrush 10 includes a plastic body having a handle 12 and a head 14 attached to a bristle portion 16. Also attached to the head at the base of the bristles is 30 template 20, a sustained-release matrix.

The body of the toothbrush is formed by conventional methods well-known in the art. The handle is shaped to be grasped by a hand, but alternatively can be shaped to fit into an electric toothbrush. The configuration of the head can vary and may be oval, convex curved, flat trim, or serrated V, or any other desired configuration.

- 8 -

The shape and size of handle 12 and head 14 can vary and the axes of the handle and head may be on the same or a different plane. The bristle portion is formed of tufts of individual filaments attached to the head in manners known to the art. Preferred filaments are those formed of polyamide and polyester. The filaments preferably have substantially uniform longitudinal lengths of between 0.3 and 6 cm, and substantially uniform cross-sectional dimensions between about 110 to about 350 microns.

There are three types of preferred templates.

1. Single-layer template including chlorhexidine

The single-layer template consists of a resin, ethylene vinyl acetate; a water-soluble polymer, Polyox; and an anti-microbial agent, chlorhexidine digluconate.

the matrix and has negligible solubility in water.

It provides the matrix with its structural integrity when the other components of the matrix leach out during use. Ethylene vinyl acetate has low toxicity and grades are available that have low processing temperatures. Importantly, ethylene vinyl acetate maintains the integrity of the matrix without becoming stiff and brittle.

than 50 percent by weight, of ethylene vinyl
acetate should be included in the matrix so that
when the other components leach out there is still
enough resin present to maintain the structure of
the matrix. Of course, not so much should be
included that the matrix cannot be loaded with a
sufficient amount of the water-soluble polymer and
anti-microbial agent; preferably, the matrix should
include less than 90 percent of the ethylene vinyl

- 9 -

acetate by weight.

The ethylene vinyl acetate polymer used in the matrix preferably should contain between 5 percent and 50 percent by weight vinyl acetate. If the polymer includes too little vinyl acetate, the matrix may be too stiff and require higher processing temperatures. If the polymer includes too much vinyl acetate, the matrix may be rubberlike and too soft to process.

Polyox water-soluble resins are non-ionic ethylene oxide homopolymers that range in molecular weight from about 100,000 and 5,000,000. Polyox has a very low degree of toxicity, and grades are available that have a low processing temperature, and are completely water soluble in cold and warm water.

The preferred Polyox, available from DuPont, is WSR N-750, which has a molecular weight of 300,000. WSR N-750 has a water solubility that is sufficient to provide a controlled-release of the anti-microbial agent from the matrix at bactericidal levels, but the solubility in the matrix is low enough that it dissolves out slowly, over a period of many uses.

25 The matrix preferably contains between 5 percent and 40 percent Polyox WSR N-750 by weight. If too much Polyox is included, the anti-microbial agent may leach out too quickly, and the structural integrity of the matrix once most of the Polyox has leached out may be adversely affected. If too little Polyox is included, too low a quantity of the anti-microbial agent may be released from the matrix during use.

The preferred anti-microbial agent is

35 chlorhexidine digluconate, which is well-known for its gingivitis-prevention properties. The amount of chlorhexidine included in the matrix depends on

the level of the desired dosage and amount of Polyox; preferably, the matrix includes between 1 percent and 30 percent of chlorhexidine digluconate by weight. If too high a level of chlorhexidine is included, the matrix may become brittle. Of course, a sufficient amount of the agent should be included so that enough is released during use to be effective.

The template should be formed to fit to

the shape of the head at the base of the bristles,
and should be as thick as possible to allow for
many uses before all of the anti-microbial agent is
leached out. Preferably, the template is at least
0.5 mm thick to ensure adequate mechanical

strength, and can be up to at least 4 mm thick.

In use, the toothbrush is rinsed with water, toothpaste applied, and then the head of the brush is inserted into the mouth to brush the teeth with the bristles. Upon contact with water some of the anti-microbial agent diffuses out of the matrix, onto and down the bristles, and eventually into the saliva of the mouth, killing bacteria on contact. As the Polyox slowly dissolves with repeated uses of the brush, water is allowed to penetrate into the matrix, making more of the anti-microbial agent accessible by diffusion from the matrix core. Eventually, all of the Polyox and agent have left the matrix, and the toothbrush is discarded.

30 The matrix is designed to incorporate the desired criteria of release rate, dosage, and effective template lifetime by adjusting the thickness of the template included on the brush, the quantity of anti-microbial agent contained in the matrix, and the quantity of Polyox, or other water-soluble polymer, included in the matrix. The higher the desired dosage, the greater the quantity

of water-soluble polymer and agent included in the matrix. Also, to increase the released dosage, a more water-soluble form of Polyox can be employed. The lifetime of a given matrix can be increased by increasing the thickness of the template.

Examples of preferred matrices were made by the following procedure.

Materials

a. Chlorhexidine digluconate

- A 20 percent solution of chlorhexidine digluconate, available from Pliva Pharmaceutical, Chemical, Food, and Cosmetic Industry of Zagreb, Yugoslavia, or ICI, was freeze-dried as follows:
- Measure 500 ml of chlorhexidine
 digluconate in a graduated cylinder and transfer it to a l liter flask.
 - 2. Adjust volume to 1 liter with double distilled filtered water and mix together.
- 3. Transfer 300 ml. portions of mixture 20 to glass evaporating dishes (8 inch diameter).
 - 4. Place all evaporating dishes in the freeze-drying apparatus until all water is removed.
 - 5. Transfer the chlorhexidine freezedried powder to a l liter glass bottle and cap.
- 25 6. Store the bottle in a refrigerator or a dark room at approximately 4°C.

b. Ethylene Vinyl Acetate

The most preferred ethylene vinyl acetate is sold by DuPont under the tradename ELVAX 360,

30 and has a vinyl acetate content of 25 percent by weight; a tensile strength of 18.0 Mpa at 23°C.

(ASTM D638); an elongation of 800 percent at 23°C.

(ASTM D638); a softening temperature of 53°C. (ASTM D1525); and a flexural modulus of 26 Mpa at 23°C.

35 (ASTM D790). ELVAX 360 contains 500 ppm BHT as an anti-oxidant.

In order to mix with chlorhexidine and

PCT/US92/06770 WO 93/03649

Polyox powders, ELVAX 360 pellets are ground into powders with particle sizes of less than 250 microns with a Glen Mill Granulator (Model #CS 150/100-2) installed with a screen plate having 1 5 mm screen holes. A suction system is added to the grinding chamber to facilitate the removal of powders from the chamber to a container. During grinding, the material is recycled through the grinder as many times as necessary (usually two or 10 three passes) to meet the size requirement. A sieve shaker manufactured by the W.S. Tyler Co. is used to control the sizes as needed.

c. Polyox

20

30

Polyox WSR N-750 is available from Union 15 Carbide, and has a melting point of 62-67°C. and a molecular weight of 300,000. The Polyox is used as received and mixed with other components to form the template.

d. Blending of Materials

The ELVAX 360, Polyox, and chlorhexidine digluconate are mixed in a blender. Each component is first weighed and then poured into a glass jar with a capacity of 0.5 kilograms. The jar is then placed on a ball-mill rotator and mixed for 25 approximately 1/2 hour. For a quantity greater than 0.5 kilograms, a V-blender manufactured by Patterson-Kelly Co. Inc. is used. The blended material should be stored in a dry, cool room.

e. Processing

The conventional equipment used to produce the matrix includes an extruder, a cooling plate, and a puller. An extrusion die with an opening of 2" wide is used. To control the thickness of the template, the die utilizes a 35 flexible lip design which enables the die lip to be adjusted anywhere from 0.15" to 0.45". Each die is supplied with a sensor for the recording of melt

- 13 -

pressure and temperature. Pulling speed are adjusted to produce a 1" wide strip with a thickness of 0.020" or 0.040". The strip can then be fabricated into templates.

and single-screw extruder. The Werner & Pfleiderer 30mm twin-screw extruder is based on a corotating and intermeshing twin-screw system. To minimize Polyox and chlorhexidine degradation during processing, the twin screws consists of only two high-shear kneading elements and the rest being low-shear conveying screw elements; the screw speed and processing temperatures are reduced to a minimum. The mixture is fed using a K-Tron twin-screw feeder (Model T20).

Alternatively, a Haake 3/4 inches singlescrew extruder equipped with a 5HP drive motor is
employed. When making the most preferred matrix,
the extruder was operated with a screw speed of 35
rpm, a barrel pressure of 70 psi, a die pressure of
80 psi, barrel temperature of 113°C., and a die
temperature of 113°C.

The blend of materials is fed to either extruder and the strip produced is pulled onto a plate by a Farris puller at a speed of between three or four feet per minute with minimum tension on the strip. The strip is cooled on a plate placed inside a PVC tube by blowing dry compressed air into the tube at approximately 10 CFM. The finished product should be kept in a cool, dry room.

The matrices can also be made by other conventional processes, such as by injection molding, casting foam dispensing machines, and reaction injection molding. In addition, two color injection molding can be used to make the toothbrush/matrix combination.

- 14 -

Toothbrush Preparation

Toothbrushes including the sustainedrelease matrix were prepared according to the following procedure:

- 1. Toothbrush handles with undercuts on the toothbrush head for placing templates were molded.
- 2. The strips prepared above were cut into two strips having maximum width of 39/64".10 Tape was used to hold the material to prevent stretching.
 - 3. Sets of holes corresponding to the desired bristle pattern to be used with the brush were punched with a Dake arbor press.
- 15 4. Templates of the desired size were cut from the strips, and glued to the head of the toothbrush body.
 - 5. The bristles were attached to the head by standard procedures.

20 Testing for Sustained-Release Properties

The sustained-release matrices of the invention can be tested for their long-term release profiles according to the following procedure.

First, a calibration plot of

25 chlorhexidine digluconate in distilled water was
prepared over concentration range of 2 to 40
mcg/ml. Release studies were performed in
triplicate; the procedure is summarized below:

- 1. Samples $(1/2" \times 1")$ were cut from the 30 strip by random sampling.
 - 2. The samples were placed in 250 ml beakers, which were then set into a shaking water bath (37°C., 80 rpm).
- 3. 5 ml of distilled water were pipetted 35 to each beaker.
 - 4. After 5 minutes, the samples were removed from beakers and assayed for chlorhexidine

- 15 -

content in release solution by uv-spectrophotometric analysis.

5. This procedure was repeated for 100 release periods.

The preferred strips showed excellent 5 chlorhexidine release characteristics over extended periods of use. The composition of the preferred strips, and their release properties after 100 uses, are summarized in the Table below. In the 10 Table, EVA is the preferred ethylene vinyl acetate discussed above; the Polyox is either the more preferred WSR N-750, or a 60:40 blend (60% Polyox coagulant grade, 40% WSR N-750 from Union Carbide); CHG is chlorhexidine digluconate; "S" means the 15 template was prepared by single-screw extrusion, "T" by twin-screw extrusion; [CHG] (ppm) is the concentration of CHG in ppm in the release solution at 100 releases and 60m (60 mesh) or 18m (18 mesh) is the particle size of chlorhexidine digluconate 20 employed (no particle size listing indicates that the chlorhexidine was not sieved following freezedrying). All of the templates were still releasing over 1 ppm chlorhexidine after 100 uses. The most preferred matrix is 2mm thick and includes 60% EVA, 25 15% Polyox WSR N-750, and 25% chlorhexidine digluconate.

Type		Thickness (mm)	Composition (%)					(ppm)	
\$\begin{array}{c c c c c c c c c c c c c c c c c c c			EVA	Pol	yox	CHG			
\$\begin{array}{c c c c c c c c c c c c c c c c c c c		_			(60-40)	75	TOT	c	5.51
1.0 70 15 (N-750) 15 ICI S 20 0.5 70 15 (60:40) 15 ICI S 1 0.5 70 15 (N-750) 15 ICI S 1 0.5 70 15 (N-750) 15 ICI S 2 10 0.5 70 15 (N-750) 15 ICI S 2 11 0.5 70 15 (N-750) 15 ICI S 2 11 0.5 70 15 (N-750) 15 ICI S 2 11 0 65 20 (N-750) 15 ICI S 3 11 0 60 25 (N-750) 15 ICI S 3 11 0 60 25 (N-750) 15 ICI S 12 11 0 70 15 (N-750) 15 ICI S 7 11 0 70 15 (N-750) 15 ICI T 7 15 1.0 70 15 (N-750) 15 ICI T 7 15 1.0 70 15 (N-750) 15 ICI T 7 16 1.0 70 15 (N-750) 15 ICI T 7 17 1.0 70 15 (N-750) 15 ICI T 7 18 1.0 70 15 (N-750) 15 ICI T 23 18 1.0 70 15 (N-750) 15 ICI T 23 18 1.0 70 15 (N-750) 15 ICI T 23 18 1.0 70 15 (N-750) 15 ICI T 24 18 10 70 15 (N-750) 15 ICI T 9 19 10 10 10 10 10 10 10 10 10 10 10 10 10	_								6.49
0.5 70 15 (60:40) 15 ICI S 1 0.5 70 15 (N-750) 15 ICI S 1 0.5 70 15 (N-750) 15 ICI S 2 10 0.5 70 15 (N-750) 15 ICI S 2 11.0 65 20 (N-750) 15 ICI S 8 1.0 60 25 (N-750) 15 ICI S 12 1.0 50 35 (N-750) 15 ICI S 12 1.0 70 15 (N-750) 15 ICI S 12 1.0 70 15 (N-750) 15 ICI S 7 1.0 70 15 (N-750) 15 ICI S 7 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 10 (N-750) 20 ICI T 21 2.0 65 15 (N-750) 20 (60m ICI) S 17 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 70 15 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 64 2.0 60 15 (N-750) 25 (ICI) T 31	5								20.98
0.5 70 15 (N-750) 15 ICI S 1 0.5 70 15 (N-750) 15 ICI S 2 10 0.5 70 15 (N-750) 15 ICI S 2 1.0 65 20 (N-750) 15 ICI S 8 1.0 60 25 (N-750) 15 ICI S 12 1.0 50 35 (N-750) 15 ICI S 12 1.0 50 35 (N-750) 15 ICI S 7 1.0 70 15 (N-750) 15 ICI S 7 1.0 70 15 (N-750) 15 ICI T 2 1.0 70 15 (N-750) 15 ICI T 2 1.0 70 15 (N-750) 15 ICI T 2 1.0 70 10 (N-750) 20 ICI T 2 1.0 70 10 (N-750) 20 ICI T 21 2.0 65 15 (N-750) 15 (60m ICI) S 17 2.0 70 15 (N-750) 15 (60m ICI) S 17 2.0 70 15 (N-750) 15 (60m ICI) S 12 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 10 (N-750) 15 (60m ICI) T 9 2.0 65 10 (N-750) 15 (60m ICI) T 9 2.0 65 10 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 25 (60m ICI) T 50 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 55 10 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) T 15 2.0 60 15 (N-750) 25 (10m ICI) T 29 2.0 60 15 (N-750) 25 (10m ICI) T 15 2.0 60 15 (N-750) 25 (10m ICI) T 15 2.0 60 15 (N-750) 25 (10m ICI) T 22 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31									1.32
0.5 70 15 (N-750) 15 ICI S 2 1.0 0.5 70 15 (N-750) 15 ICI S 2 1.0 65 20 (N-750) 15 ICI S 8 1.0 60 25 (N-750) 15 ICI S 12 1.0 50 35 (N-750) 15 ICI S 12 1.0 70 15 (N-750) 15 ICI S 7 1.0 70 15 (N-750) 15 ICI T 7 1.0 70 10 (N-750) 15 ICI T 2 1.0 70 10 (N-750) 20 ICI T 2 1.0 70 10 (N-750) 20 ICI T 21 2.0 65 15 (N-750) 15 (Om ICI) S 17 2.0 70 15 (N-750) 15 (Om ICI) S 12 2.0 70 15 (N-750) 15 (Om ICI) S 12 2.0 70 15 (N-750) 15 (Om ICI) S 12 2.0 70 15 (N-750) 15 (Om ICI) S 11 2.0 70 15 (N-750) 15 (Om ICI) S 11 2.0 70 15 (N-750) 15 (Om ICI) S 11 2.0 70 15 (N-750) 15 (Om ICI) S 11 2.0 70 15 (N-750) 15 (Om ICI) T 9 2.0 65 20 (N-750) 15 (Om ICI) T 9 2.0 65 15 (N-750) 15 (Om ICI) T 9 2.0 65 15 (N-750) 20 (Om ICI) T 9 2.0 65 15 (N-750) 25 (Om ICI) T 50 2.0 60 15 (N-750) 25 (Om ICI) T 7 2.0 60 15 (N-750) 25 (Om ICI) T 7 2.0 60 15 (N-750) 25 (Om ICI) T 7 2.0 60 15 (N-750) 25 (Om ICI) S 63 2.0 55 10 (N-750) 25 (Om ICI) S 63 2.0 55 10 (N-750) 25 (Om ICI) S 63 2.0 60 15 (N-750) 25 (Om ICI) S 63 2.0 60 15 (N-750) 25 (Om ICI) S 63 2.0 60 15 (N-750) 25 (Om ICI) S 63 2.0 60 15 (N-750) 25 (Om ICI) S 63 2.0 60 15 (N-750) 25 (ICI) S 64 2.0 60 15 (N-750) 25 (ICI) S 54 2.0 60 15 (N-750) 25 (ICI) T 31									1.57
10 0.5 70 15 (N-750) 15 ICI S 2 1.0 65 20 (N-750) 15 ICI S 8 1.0 60 25 (N-750) 15 ICI S 12 1.0 50 35 (N-750) 15 ICI S 7 1.0 70 15 (N-750) 15 ICI T 2 1.0 70 10 (N-750) 15 ICI T 2 1.0 70 10 (N-750) 15 ICI T 2 1.0 70 10 (N-750) 15 ICI T 2 2.0 65 15 (N-750) 20 ICI T 2 2.0 65 15 (N-750) 15 (Pliva) S 12 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 70 15 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 25 (60m ICI) T 50 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 63 2.0 60 15 (N-750) 25 (10m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) S 64									2.19
1.0 65 20 (N-750) 15 ICI S 8 1.0 60 25 (N-750) 15 ICI S 12 1.0 50 35 (N-750) 15 ICI S 7 1.0 70 15 (N-750) 15 ICI T 7 1.0 70 15 (N-750) 15 ICI T 7 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 10 (N-750) 20 ICI T 21 2.0 65 15 (N-750) 20 (60m ICI) S 17 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 70 15 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (18m ICI) S 6 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 25 (60m ICI) T 9 2.0 65 15 (N-750) 25 (60m ICI) T 50 2.0 65 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31 2.0 60 15 (N-750) 25 (10m ICI) T 31									2.53
1.0 60 25 (N-750) 15 ICI S 12 1.0 50 35 (N-750) 15 ICI S 7 1.0 70 15 (N-750) 15 ICI T 7 1.0 70 15 (N-750) 15 ICI T 7 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 10 (N-750) 20 ICI T 21 2.0 65 15 (N-750) 20 (60m ICI) S 17 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 65 20 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 60 15 (N-750) 15 (60m ICI) T 9 2.0 60 15 (N-750) 20 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 55 10 (N-750) 25 (60m ICI) S 63 2.0 55 10 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 62 2.0 60 15 (N-750) 25 (10m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) S 64 2.0 60 15 (N-750) 25 (10m ICI) S 64	10								8.63
1.0 50 35 (N-750) 15 ICI S 7 1.0 70 15 (N-750) 15 ICI T 7 15 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 10 (N-750) 20 ICI T 21 2.0 65 15 (N-750) 20 (60m ICI) S 17 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 65 20 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 3.0 60 15 (N-750) 25 (60m ICI) T 7 3.0 60 15 (N-750) 25 (60m ICI) T 7 3.0 60 15 (N-750) 25 (60m ICI) T 7 3.0 60 15 (N-750) 25 (60m ICI) T 7 3.0 60 15 (N-750) 25 (60m ICI) S 63 3.0 60 15 (N-750) 25 (60m ICI) S 63 3.0 60 15 (N-750) 25 (60m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 64									12.41
1.0 70 15 (N-750) 15 ICI T 7 7 15 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 10 (N-750) 20 ICI T 21 2.0 65 15 (N-750) 20 ICI T 21 2.0 70 15 (N-750) 20 (60m ICI) S 17 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 65 20 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11. 2.0 70 15 (N-750) 15 (60m ICI) S 11. 2.0 70 15 (N-750) 15 (60m ICI) S 6. 2.0 70 15 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 65 10 (N-750) 15 (60m ICI) T 9. 2.0 65 10 (N-750) 15 (60m ICI) T 9. 2.0 65 15 (N-750) 25 (60m ICI) T 50. 2.0 65 15 (N-750) 25 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 2.0 60 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 60 15 (N-750) 25 (18m ICI) S 63. 2.0 60 15 (N-750) 25 (18m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 62. 2.0 60 15 (N-750) 25 (19m ICI) S 62. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 63. 2.0 60 15 (N-750) 25 (19m ICI) S 64. 2.0 60 15 (N-750) 25 (10m ICI) T 31. 2.0 60 15 (N-750) 25 (10m ICI) T 31. 2.0 60 15 (N-750) 25 (10m ICI) T 31. 2.0 60 15 (N-750) 25 (10m ICI) T 31.									7.04
15 1.0 70 15 (N-750) 15 ICI T 23 1.0 70 15 (N-750) 15 ICI T 2 1.0 70 10 (N-750) 20 ICI T 21 2.0 65 15 (N-750) 20 (60m ICI) S 17 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 65 20 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 6. 2.0 70 15 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 65 15 (N-750) 15 (60m ICI) T 9. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 30 2.0 65 15 (N-750) 25 (60m ICI) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 55 15 (N-750) 25 (60m ICI) S 63. 2.0 60 15 (N-750) 25 (18m ICI) S 63. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 35 2.0 60 15 (N-750) 25 (18m ICI) S 62. 36 2.0 60 15 (N-750) 25 (18m ICI) S 62. 37 2.0 60 15 (N-750) 25 (18m ICI) S 62. 38 2.0 60 15 (N-750) 25 (18m ICI) S 62. 39 2.0 60 15 (N-750) 25 (18m ICI) S 62. 30 60 15 (N-750) 25 (Pliva) T 29. 30 2.0 60 15 (N-750) 25 (Pliva) S 72. 31 2.0 60 15 (N-750) 25 (ICI) S 54. 32.0 60 15 (N-750) 25 (ICI) S 54. 35 2.0 60 15 (N-750) 25 (ICI) S 54.									7.84
1.0 70 15 (N-750) 15 ICT T 2 1.0 70 10 (N-750) 20 ICT T 21 2.0 65 15 (N-750) 15 (Pliva) S 17 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 65 20 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 6 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 15 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) T 50 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 30 2.0 60 15 (N-750) 25 (60m ICI) T 7 30 2.0 60 15 (N-750) 25 (60m ICI) T 7 30 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 55 10 (N-750) 25 (60m ICI) S 63 2.0 55 10 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (Pliva) T 29 3.0 60 15 (N-750) 25 (Pliva) T 29 3.0 60 15 (N-750) 25 (ICI) S 54 3.0 60 15 (N-750) 25 (ICI) T 31									23.15
1.0 70 10 (N-750) 20 ICI T 21 2.0 65 15 (N-750) 20 (60m ICI) S 17 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 65 20 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 60 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 15 (N-750) 25 (60m ICI) T 50 2.0 60 15 (N-750) 25 (60m ICI) T 50 2.0 65 15 (N-750) 25 (60m ICI) T 7 3.0 2.0 60 15 (N-750) 25 (60m ICI) T 7 3.0 2.0 60 15 (N-750) 25 (60m ICI) T 7 3.0 2.0 60 15 (N-750) 25 (60m ICI) T 7 3.0 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 55 10 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) S 63 3.0 60 15 (N-750) 25 (60m ICI) S 63 3.0 60 15 (N-750) 25 (18m ICI) S 62 3.0 60 15 (N-750) 25 (19liva) T 15 3.0 60 15 (N-750) 25 (19liva) T 29 3.0 60 15 (N-750) 25 (19liva) S 72 3.0 60 15 (N-750) 25 (19liva) T 29 3.0 60 15 (N-750) 25 (171) S 54 3.0 60 15 (N-750) 25 (ICI) T 31 3.0 60 15 (N-750) 25 (ICI) S 64	15								2.73
2.0 65 15 (N-750) 20 (60m ICI) S 17 2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 65 20 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 60 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (Pliva) T 1 2.0 60 15 (N-750) 25 (60m ICI) T 50 2.0 65 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 30 2.0 60 15 (N-750) 25 (60m ICI) T 7 30 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 55 10 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (19m ICI) S 62 2.0 60 15 (N-750) 25 (19m ICI) S 62 2.0 60 15 (N-750) 25 (19m ICI) S 62 2.0 60 15 (N-750) 25 (19m ICI) S 62 2.0 60 15 (N-750) 25 (19m ICI) S 62 2.0 60 15 (N-750) 25 (19m ICI) S 62 2.0 60 15 (N-750) 25 (19m ICI) S 62 2.0 60 15 (N-750) 25 (19m ICI) S 54 2.0 60 15 (N-750) 25 (10m ICI) S 54 2.0 60 15 (N-750) 25 (ICI) S 54									21.38
2.0 70 15 (N-750) 15 (Pliva) S 12 2.0 65 20 (N-750) 15 (60m ICI) S 7 2.0 70 15 (N-750) 15 (60m ICI) S 11 2.0 70 15 (N-750) 15 (60m ICI) S 6 2.0 70 15 (N-750) 15 (60m ICI) S 6 2.0 70 15 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 65 20 (N-750) 15 (60m ICI) T 9 2.0 60 15 (N-750) 25 (60m ICI) T 50 2.0 60 15 (N-750) 25 (60m ICI) T 7 2.0 60 15 (N-750) 25 (60m ICI) T 7 30 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 55 15 (N-750) 30 (60m Pliva) T 7 30 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (60m ICI) S 63 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (18m ICI) S 62 2.0 60 15 (N-750) 25 (Pliva) T 29 3.0 60 15 (N-750) 25 (Pliva) S 72 3.0 60 15 (N-750) 25 (Pliva) S 72 3.0 60 15 (N-750) 25 (ICI) S 54 3.0 60 15 (N-750) 25 (ICI) S 54 3.0 60 15 (N-750) 25 (ICI) T 31 3.0 60 15 (N-750) 25 (60m Pliva) T 29 3.0 60 15 (N-750) 25 (ICI) S 54 3.0 60 15 (N-750) 25 (ICI) T 31									17.59
2.0 65 20 (N-750) 15 (60m ICI) S 7. 2.0 70 15 (N-750) 15 (60m ICI) S 11. 2.0 70 15 (N-750) 15 (18m ICI) S 6. 2.0 70 15 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 60 15 (N-750) 25 (60m ICI) T 50. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 30 2.0 60 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 35 (60m ICI) S 63. 2.0 55 10 (N-750) 35 (60m ICI) S 63. 2.0 60 15 (N-750) 25 (18m ICI) S 63. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 36 2.0 60 15 (N-750) 25 (Pliva) S 72. 37 2.0 60 15 (N-750) 25 (Pliva) S 72. 38 2.0 60 15 (N-750) 25 (ICI) S 54. 39 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (ICI) T 31. 30 2.0 60 15 (N-750) 25 (ICI) T 31.									12.43
2.0 70 15 (N-750) 15 (60m ICI) S 11. 2.0 70 15 (N-750) 15 (18m ICI) S 6. 2.0 70 15 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 60 15 (N-750) 25 (60m ICI) T 50. 2.0 65 15 (N-750) 20 (60m ICI) T 7. 2.0 60 15 (N-750) 20 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 30 2.0 55 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 35 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 36 2.0 60 15 (N-750) 25 (Pliva) T 29. 37 2.0 60 15 (N-750) 25 (Pliva) T 29. 38 2.0 60 15 (N-750) 25 (ICI) S 54. 39 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 30 2.0 60 15 (N-750) 25 (ICI) T 31.	20								7.62
2.0 70 15 (N-750) 15 (18m ICI) S 6. 2.0 70 15 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 60 15 (N-750) 25 (60m ICI) T 50. 2.0 60 15 (N-750) 20 (60m ICI) T 7. 2.0 60 15 (N-750) 20 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 2.0 55 15 (N-750) 30 (60m Pliva) T 9. 2.0 55 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 35 (60m ICI) S 63. 2.0 60 15 (N-750) 25 (18m ICI) S 63. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 35 2.0 60 15 (N-750) 25 (19liva) S 72. 36 2.0 60 15 (N-750) 25 (Pliva) S 72. 37 2.0 60 15 (N-750) 25 (Pliva) T 29. 38 2.0 60 15 (N-750) 25 (ICI) S 54. 39 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (ICI) T 31.	20								11.20
2.0 70 15 (N-750) 15 (60m ICI) T 9. 2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 70 15 (N-750) 15 (Pliva) T 1. 2.0 60 15 (N-750) 25 (60m ICI) T 50. 2.0 65 15 (N-750) 20 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m Pliva) T 9. 2.0 55 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 55 10 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (ICI) T 31.									6.78
2.0 65 20 (N-750) 15 (60m ICI) T 9. 2.0 70 15 (N-750) 15 (Pliva) T 1. 2.0 60 15 (N-750) 25 (60m ICI) T 50. 2.0 65 15 (N-750) 20 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m Pliva) T 9. 2.0 55 15 (N-750) 30 (60m Pliva) T 9. 2.0 55 15 (N-750) 35 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (18m ICI) S 63. 2.0 60 15 (N-750) 25 (60m (Pliva) T 15. 2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (ICI) T 31.									9.10
2.0 70 15 (N-750) 15 (Pliva) T 1. 2.0 60 15 (N-750) 25 (60m ICI) T 50. 2.0 65 15 (N-750) 20 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m Pliva) T 9. 2.0 55 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 55 10 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (19liva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) S 72. 36 2.0 60 15 (N-750) 25 (Pliva) T 29. 37 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (ICI) T 31.									9.08
2.0 60 15 (N-750) 25 (60m ICI) T 50. 2.0 65 15 (N-750) 20 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m Pliva) T 9. 2.0 55 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 55 10 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (ICI) T 31.	25								1.53
2.0 65 15 (N-750) 20 (60m ICI) T 7. 2.0 60 15 (N-750) 25 (60m Pliva) T 9. 2.0 55 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 55 10 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) S 61.	23								50.76
2.0 60 15 (N-750) 25 (60m Pliva) T 9. 2.0 55 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 55 10 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (ICI) T 31.									7.67
2.0 55 15 (N-750) 30 (60m Pliva) T 7. 30 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 55 10 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (60m Pliva) S 61.								T	9.83
30 2.0 60 15 (N-750) 25 (60m ICI) S 63. 2.0 55 10 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31.								T	7.10
2.0 55 10 (N-750) 35 (60m Pliva) T 15. 2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (60m Pliva) S 61.	30								63.00
2.0 60 15 (N-750) 25 (18m ICI) S 62. 2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (60m Pliva) S 61.	30							T	15.78
2.0 60 15 (N-750) 25 (60m (Pliva) 47. 2.0 60 15 (N-750) 25 (Pliva) S 72. 35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (60m Pliva) S 61.								S	62.34
2.0 60 15 (N-750) 25 (Pliva) S 72. 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (60m Pliva) S 61.									47.22
35 2.0 60 15 (N-750) 25 (Pliva) T 29. 2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (60 Pliva) S 61.								S	72.63
2.0 60 15 (N-750) 25 (ICI) S 54. 2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (60m Pliva) S 61.	35						(Pliva)	T	29.72
2.0 60 15 (N-750) 25 (ICI) T 31. 2.0 60 15 (N-750) 25 (60m Pliva) S 61.	55							S	54.56
2.0 60 15 (N-750) 25 (60m Pliva) S 61.								T	31.37
							(60m Pliva)	S	61.24
2.U 50 15 (N-750) 25 (COM F11Vd) 5 CO		2.0	60	15	(N-750)	25	(60m Pliva)	S	60.03
						25	(60m Pliva)	S	60.43

2. Two-layer template including chlorhexidine

The preferred single-layer template generally includes over 50% support resin (EVA) by weight to achieve good mechanical properties and 5 processibility. This, to some extent, limits the quantity of chlorhexidine that can be included in the matrix. An alternative two-layer template provides a higher quantity of chlorhexidine in the portion of the template that primarily contacts 10 water and saliva. The first, outer layer contains less ethylene vinyl acetate and more polyethylene oxide and chlorhexidine. The second, inner layer has the composition of the preferred single-layer embodiment, although the second layer could consist 15 entirely of ethylene vinyl acetate. A preferred two-layer matrix includes 65% ethylene vinyl acetate, 15% Polyox, and 20% chlorhexidine digluconate in the inner layer, and 30% ethylene vinyl acetate, 25% Polyox, and 45% chlorhexidine 20 digluconate in the outer layer. The inner layer should include at least 60% of the support resin; the outer layer can include upwards of 50% chlorhexidine.

The outer layer releases a higher dosage
25 of chlorhexidine when contacted with water, yet has
good strength and processibility because the second
layer provides the necessary support. As the outer
layer wears away, the anti-microbial agent in the
inner layer also is released. The outer layer
30 preferably is 0.25 to 3 mm thick, while the inner
layer preferably is 0.1 to 0.5 mm thick.

The two-layer templates can be produced either by conventional co-extrusion or co-injection molding techniques, from two different mixtures.

35 Alternatively one layer can be extruded and then the other layer can be thermoformed/compression molded or laminated onto the extruded layer.

PCT/US92/06770 WO 93/03649

An alternative two-layer embodiment has an outer layer consisting only of the support resin and the anti-microbial agent. The preferred antimicrobial agent, chlorhexidine digluconate, is 5 water-soluble, although not to the same degree as the water-soluble polyethylene oxide. Because the outer layer includes a high quantity of the antimicrobial agent, enough of the agent can dissolve out of the matrix to provide a sufficient dosage of 10 the agent without the assistance of a water-soluble polymer.

Template including a colorant 3.

The wear-indicator template preferably includes two layers, each with a different 15 colorant. The outer layer includes a water-soluble polymer (preferably polyethylene oxide, polyethylene glycol, or polyvinyl alcohol) and a colorant, preferably a water-leachable colorant; a support resin is optional. The inner layer 20 includes a support resin and a second colorant, like titanium dioxide, which provides a solid white appearance. The different colorants should be selected to provide a clear contrast so that a user can plainly discern the color change as the 25 colorant in the outer layer leaches out over time. The two-layer templates including a colorant can be produced by the same techniques used to produce the two-layer templates including

The preferred wear-indicating template is illustrated in Fig. 2a and consists of an outer layer 22, which includes the colorant that is released during use, and an inner layer 24, which is adjacent the toothbrush during use. Inner layer 35 24 includes titanium dioxide.

an anti-microbial agent discussed above.

30

Alternative two-layer template embodiments are illustrated in Figs. 2b-2f. In these embodiments, no colorant is included in the outer layer 26 and a non-white colorant is included in the inner layer 28. The outer layer in these embodiments preferably consists only of water-soluble polymer; as the outer layer dissolves away during use the colorant in the second layer becomes visible, or more visible, providing an indication of the degree of wear of the brush.

Referring to Fig. 2b, a template has a

10 flat outer layer 26 and a flat inner layer 28 that
are approximately the same size. As outer layer 26
dissolves away with repeated use, a colorant in
inner layer 28 becomes visible to a user looking
straight down at the surface of the bristles that

15 contact the teeth.

Referring to Fig. 2c, inner layer 28 of a template has elements 30 that extend into grooves in outer layer 26. As outer layer 26 dissolves away, elements 30, which include colorant, become visible to the user as stripes at the base of the bristles. A similar embodiment is illustrated in Fig. 2d, except that elements 32 extend along the exterior of outer layer 26. In this embodiment, as outer layer 26 dissolves away a colored strip along the edge of the template becomes visible to a user looking straight down at the surface of the bristles that contact the teeth.

Referring to Figs 2e and 2f, an alternative template includes an inner layer 28

30 that is fully surrounded by the outer layer 26 except at surface 34, where the template is attached to the head of the brush. As outer layer 26 dissolves, inner layer 28 becomes visible from the sides and from the top.

Although not illustrated, other alternative matrices include those in which the inner layer(s) is simply two narrow strips, like

elements 30; and those in which the inner layer includes cylindrical elements that extend upwards from the inner layer into the outer layer. In the latter embodiment, as the outer layer dissolves away the inner layer becomes visible as colored dots.

The following examples were made from two 3/4 inch extruders with a co-extrusion die to produce two-layer templates having the design shown in Fig. 2a and having a thickness of about 10 mm.

Example A

The first layer of the template consisted of 44.6% ethylene vinyl acetate (Elvax 360), 44.5% Polyox N-750, 10% polyethylene glycol (Dow-E4500), and 0.9% of a dark blue pigment (FD&C Blue No. 2, Aluminum Lube 35-42%, available from Warner Jenkinson of St. Louis, MO). The second layer consisted of 99.5% Elvax 360 and 0.5% titanium dioxide. When the template was submerged in water for 24-hours, the initial dark blue color changed to a light blue.

Example B

The first layer of the template includes 49.5% Elvax 360, 49.5% Polyox N-750, and 1% dark blue pigment. The second layer was the same as in Example A. The results of a 24-hour water-submerge test also were the same.

Example C

The first layer of the template consists

of 99% polyvinyl alcohol and 1% of the dark blue pigment, and no support resin. The second layer was the same as for the other two examples. When this template was subjected to a 24-hour water-submerge test, the initial dark blue color of the template turned to white.

Other Embodiments

Other embodiments are within the claims.

For example, other water-insoluble polymers can be used as the support resin. To determine whether a polymer can be used as a support resin within the meaning of this application, a template should be 5 prepared containing 60% of the polymer, 15% Polyox WSR N-750, and 25% chlorhexidine digluconate. Matrix samples (1/2" x 1") having a thickness of 2 mm are placed in 250 ml beakers which are then set into a shaking water bath 10 (37°C., 80 rpm) for 8 hours. If the matrix has maintained its structural integrity in the bath and does not fall apart, the polymer is a support resin. Examples of the specific polymers that can be used in place of EVA as the support resins 15 include Hytrel G-4074 (a polyester available from DuPont); Hytrel 4056 (a polyester elastomer also available from DuPont); Vestenamer 8012 (TPE, available from Huls America); Rimplast PSW 2159 (a silicone, available from Petrarch Systems); 20 Prolytropes (an ethylene/propylene alloy available from A. Schulman, Inc.); Millathanes (a polyester urethane available from Millathane); Kraton G-7680 (a styrene/rubber available from Shell Chemical); and Santoprene 101-55 (a polyolefin alloy available 25 from Monsanto Chemical). Prolytropes and Kraton G-7680 are more preferred because of their relatively low processing temperatures, 29°C. and 57°C., respectively. Examples of other general classes of polymers that can be used as support resins include 30 polyurethanes, polycarbonates, polyesters, polyethylenes, polypropylenes, polystyrenes, and polyvinyl chloride; polyurethanes, polyethylenes, and polystryenes are more preferred because forms of these polymers with relatively low processing

Additionally, other water-soluble substances can be used in place of Polyox in the

35 temperatures are available.

matrix. To determine whether something is a watersoluble substance within the meaning of this application, a template should be prepared containing 80% EVA and 20% of the substance. 5 Matrix samples (1/2" x 1") having a thickness of 2mm are placed in 250 ml beakers which are then set into a shaking water bath (37°C., 80 rpm) for 8 hours. After that time, the matrix is removed, and photomicrographs (magnification of 350X) of the 10 matrix after the procedure are compared to photomicrographs (350X) of the matrix prior to the procedure. If after the procedure channels and pores have formed into the matrix, the substance is a water-soluble substance. Other water-soluble 15 natural polymers that can be used include agar; carrageenan; corn starch; guar gum; gum arabic; gum karaya; gum tragacanth; locust bean gum; potato, wheat and rice starches; tapioca; casein; pectin; and sodium alginate. Modified natural polymers 20 that can be used include cationic starch; dextran; hydroxyalkyl starches; hydroxyethyl and hydroxypropyl cellulose; methyl cellulose; sodium carboxymethyl cellulose; xanthan gum; gelatin; and sodium carboxymethyl starch. Synthetic polymers 25 suitable for use include polyvinyl alcohol; cationic resins and quaternary ammonium compounds; poly (N-vinyl-2-pyrrolidinone); vinyl ether polymers; styrene-maleic anhydride copolymers; ethylene-maleic anhydride copolymer; hydrophilic

Anti-microbial agents that can be used in place of chlorhexidine digluconate include

35 antibiotics such as actinobolin, chlortetracycline, tetracycline, streptomycin, kanamycin, neomycin, niddamycin, bacitracin, erythromycin, penicillin,

Inorganic salts, (e.g., EDTA, NaCl, Na₂CO₃ and KCl)

30 gels; and polymeric surface-active agents.

and fillers may also be used.

rancemycin, gramicidin, saramycin, and polymyxin B; as well as antiplaque enzymes such as mucinases, pancreatin, fungal enzymes, protease-amylase, dextranase, moimnase, zendium, amyloglucosidase, and glucose oxidase. Other conventional antimicrobials that can be used include phenolic compounds (e.g., phenol, thymol, 2-phenylphenol, hexylresorcinol), and listerine (thymol, eucalyptol, menthol, methylsalicylate); bipyridines (e.g., octenidene); pyrimidines (e.g.,

pyridines (e.g., octenidene); pyrimidines (e.g., hexetidine); halogens (e.g., iodine, iodophores, fluorides); quaternary ammonium salts (e.g., cetylpyridinium chloride, benzethonium chloride, domiphen bromide); oxygenating agents (e.g.,

peroxides; perborate); herbal extracts (e.g.,
 sangnimarine); heavy metal salts (e.g., silver,
 mercury, zinc, copper, tin); and other bis biguanidines besides chlorhexidine (e.g.,
 alexidine). Of course, other chlorhexidine salts

like the diacetate and dihydrochloride can be used

in place of chlorhexidine digluconate.

Moreover, the matrices can be used in other ways, for example by impregnating the bristles of a toothbrush with small matrix

25 particles, by inserting the matrices into the holes the toothbrush head into which bristles are then inserted, or by coating the matrix on dental floss. The matrix also can be attached to the side of the head of the toothbrush opposite the side to which

30 the bristles are attached. Alternatively, a matrix can be designed to be inserted and left in the mouth for an extended period of time, for example as a small ring that fits around a tooth.

Templates can be designed that are

35 sustained-release but that do not release over 1

ppm chlorhexidine after 100 uses by the test

previously designed. For example, a disposable

- 24 -

toothbrush, which would be discarded after only a few uses, does not require such extended release lifetime. For the purposes of this invention, sustained-release means that the matrix still releases at least 1 ppm of the anti-microbial agent after 10 uses (more preferably after 50 uses) when tested according to the procedure described in the Preferred Embodiment section.

Any of the two-layer templates shown in 10 Figure 2 can be used to provide the sustainedrelease of an anti-microbial agent.

Further, other well-known, conventional additives such as fillers, binders, lubricants, and channeling agents can be included in the matrix,

15 although care should be taken that these additives do not adversely affect the agent release rate.

CLAIMS

- 1. An oral brush comprising:
 - a body comprising a handle and head;
 - a brush portion connected to the head of
- 5 said body; and
 - a sustained-release matrix comprising a support resin, a water-soluble substance, and an anti-microbial agent.
- 2. The oral brush of claim 1, wherein said
- 10 matrix is a template joined to said head.
 - 3. The oral brush of claim 1, wherein said resin comprises ethylene vinyl acetate.
 - 4. The oral brush of claim 1, wherein said water soluble substance comprises an organic
- 15 polymer.
 - 5. The oral brush of claim 4, wherein said polymer comprises polyethylene oxide.
 - 6. The oral brush of claim 1, wherein said anti-microbial agent comprises chlorhexidine.
- 7. The oral brush of claim 1, wherein said resin comprises ethylene vinyl acetate, said water soluble substance comprises polyethylene oxide, and said anti-microbial comprises chlorhexidine.
- 8. The oral brush of claim 2, wherein said 25 template is no greater than 4mm thick.
 - 9. The oral brush of claim 1, wherein said template comprises between 50 percent and 90 percent by weight ethylene vinyl acetate; between 5 percent and 40 percent by weight polyethylene
- 30 oxide; and between 1 percent and 30 percent by weight anti-microbial agent.
 - 10. An oral brush comprising:
 - a body including a head and a handle;
 - a brush portion attached to said head;
- 35 and
 - a sustained-release matrix comprising a polymer and an anti-microbial agent.

- 26 -

11. The oral brush of claim 10, wherein said sustained-release matrix is attached to said head.

- 12. The oral brush of claim 10, wherein said anti-microbial agent comprises chlorhexidine.
- 5 13. The oral brush of claim 10, wherein said polymer comprises a water-soluble polymer.
 - 14. The oral brush of claim 13, wherein said water-soluble polymer comprises polyethylene oxide.
 - 15. The oral brush of claim 10, wherein said
- 10 polymer comprises a support resin.
 - 16. The oral brush of claim 10, wherein said matrix comprises
 - a. a first layer including a watersoluble polymer and an anti-microbial agent, and
- b. a second layer joined with said first layer and comprising a support resin.
 - 17. The oral brush of claim 16, wherein said water-soluble polymer is polyethylene oxide.
 - 18. The oral brush of claim 15, wherein said
- 20 second layer further comprises a support resin.

 19. The oral brush of claim 18, wherein said
 - support resin is ethylene vinyl acetate.

 20. The oral brush of claim 10, wherein said matrix comprises
- a. a first layer comprises said polymer and said anti-microbial agent, wherein said polymer is a support resin, and
 - b. a second layer joined with said first layer and comprising a support resin.
- 30 21. The oral brush of claim 20, wherein said support resin comprises ethylene vinyl acetate.
 - 22. A sustained-release matrix comprising:
 a resin comprising ethylene vinyl

acetate;

a water-soluble polymer comprising polyethylene oxide; and an anti-microbial agent.

- 23. The matrix of claim 22, comprising between 50 percent and 90 percent by weight ethylene vinyl acetate; between 5 percent and 30 percent by weight polyethylene oxide; and between 3 percent and 30 percent by weight anti-microbial agent.
 - 24. The matrix of claim 22, wherein said anti-microbial agent comprises chlorhexidine.
- 25. A sustained-release matrix comprising a first layer comprising a polymer and an antimicrobial agent, and a second layer joined to the first and comprising a support resin.
- 26. The matrix of claim 25, wherein said polymer in said first layer comprises a support 15 resin.
 - 27. The matrix of claim 25, wherein said polymer in first layer comprises a water soluble polymer.
- 28. A method of releasing an anti-microbial 20 agent from an oral brush, comprising

providing an oral brush including a body with a handle and a head, a brush portion attached to said head, and a sustained-release matrix comprising a water insoluble resin, a water-soluble polymer, and an anti-microbial agent; and

contacting the portion of said brush including said matrix with water, causing said water-soluble polymer in said matrix to dissolve, thereby releasing said anti-microbial agent into said water.

- 29. The method of claim 28, further comprising inserting said portion of the brush including the matrix into the mouth of an animal, the saliva of the animal including water that
- 35 causes said water-soluble polymer to dissolve thereby releasing said anti-microbial agent into said mouth.

- 28 -

ć

3

ř

30. The method of claim 28, wherein said anti-microbial agent is chlorhexidine.

- 31. The method of claim 28, wherein said resin comprises ethylene vinyl acetate.
- 5 32. The method of claim 28, wherein said water-soluble polymer comprises polyethylene oxide.
 - 33. A method of releasing an anti-microbial agent into a mouth of an animal, comprising providing a matrix including a resin, a


water-soluble substance, and an anti-microbial
agent; and

inserting said matrix into a mouth of an animal, said matrix releasing said anti-microbial agent into said mouth.

- 15 34. The method of claim 33, wherein said resin comprises ethylene vinyl acetate.
 - 35. The method of claim 34, wherein said water-soluble substance comprises polyethylene oxide.
- 20 36. A wear-indicator oral brush, comprising a body comprising a handle and head; a brush portion connected to the head of said body; and
- a matrix that is attached to said head of said body, said matrix comprising a colorant and a water-leachable substance that leaches into water when the oral brush is used to cause said matrix to change color after repeated uses.
- 37. The oral brush of claim 36, wherein said water-leachable substance comprises a water-soluble polymer.
- 38. The oral brush of claim 37, wherein said water-soluble polymer is selected from the group consisting of polyethylene oxide, polyethylene glycol, and polyvinyl alcohol.
 - 39. The oral brush of claim 36, wherein said matrix further comprises a water-insoluble support

resin.

- 40. The oral brush of claim 39, wherein said support resin comprises ethylene vinyl acetate.
- 41. The oral brush of claim 39, wherein said 5 water-leachable substance comprises said colorant.
 - 42. The oral brush of claim 36, wherein said matrix comprises
 - a first layer comprising said water-soluble substance; and
- a second layer joined with said first layer and comprising a water-insoluble support resin.
 - 43. The oral brush of claim 42, wherein said second layer further comprises said colorant.
- 15 44. The oral brush of claim 42, wherein said first layer comprises said colorant.






Fig. 2a

Fig. 2b




Fig. 2c

Fig. 2d




Fig. 2e




Fig. 2f

SUBSTITUTE SHEET

PCT/US92/06770

		C17US92/06770		
A. C	CLASSIFICATION OF SUBJECT MATTER			
IPC(3)) :A46B 11/00			
Accordin	:424/401 424/486 15/159 15/160 15/167.1			
B. FI	ng to International Patent Classification (IPC) or to both national classification and	I IPC		
J. 11	ELDS SEARCHED			
Minimun	n documentation searched (classification system followed by classification symbols			
U.S. :	15/104.93 15/104.94 119/88 132/162 132/163 132/313 1321/319	•,		
Documen	tation searched other than minimum documentation to the extent that such document			
	de la constant de la	s are included in the fields searched		
Electronic	data base consulted during the international search (name of data base and, wher			
	Wiler	e practicable, search terms used)		
C. DO	CUMENTS CONSIDERED TO BE RELEVANT			
Category*	Citation of document with indicate			
	Citation of document, with indication, where appropriate, of the relevant particles	assages Relevant to claim No		
Y	US,A, 3,934,001 (WATSON)			
	20 JANUARY 1976	22-27, 33-35		
	See entire document			
	os same document			
Y	IIS A 4 780 220 (DAVED)			
	US,A, 4,780,320 (BAKER) 25 OCTOBER 1988	22-27 33-35		
	Social 1988	7-27 35-35		
. [See entire document			
Y	TIO 4 0 000 000			
1	US,A, 3,992,336 (FAUCHER)	22-27 3-35		
}	16 NOVEMBER 1976	22-27 3-35		
	See entire document			
_				
Y	US,A, 4,018,729 (FAUCHER ET AL)			
1	19 APRIL 1977	22-27 33-35		
İ	See entire document			
- 1	and document	1		
1				
Pare				
	documents are listed in the continuation of Box C. See patent family	annex.		
	al categories of cited documents:			
docum to be i	nent defining the general state of the art which is not considered principle or theory underly	after the international filing date or priority th the application but cited to understand the		
•	principle of theory underly	and mic suveried		
document published on or after the international filing date "X" document of particular relevance; the claimed invention cannot be considered novel or cannot be considered to involve an inventive step when the document is taken alone.				
cited t	reason (as modified)	ii aloge		
	Y document of particular rel	evance; the claimed invention cannot be		
means	combined with one or more	other much document is		
	ent published prior to the international filing date but letter the	emen at the art		
docume				
docume the pric	led completion of the se	· · · · · · · · · · · · · · · · · · ·		
documenthe prices	ual completion of the international search Date of mailing of the international	· · · · · · · · · · · · · · · · · · ·		
documenthe prices	ual completion of the international search Date of mailing of the international	onal search report		
docume the price of the actu	Date of mailing of the international search ER 1992 O 1 DEC 1993	onal search report		
document the price of the actument NOVEMB	Date of mailing of the international search ER 1992 In address of the ISA/	onal search report		
docume the price of the actu NOVEMB	Date of mailing of the international search Delta of percentage of the international search Delta of mailing of	onal search report		

Form PCT/ISA/210 (second sheet)(July 1992)*

INTERNATIONAL SEARCH REPORT

International application No. PCT/US92/06770

C (Contin	uation). DOCUMENTS CONSIDERED TO BE RELEVANT	
Category*	Citation of document, with indication, where appropriate, of the relevant passages	Relevant to claim No.
Y	US,A, 4,980,150 (KEITH) 25 DECEMBER 1990 See entire document	1,2,4,6,8,1013,1 5,16,18,20,28,30
Т	US,A, 5,061,106 (KENT) 29 OCTOBER 1991 See abstract	28,30
A	GT.BR.,A, 259,268 (GORDLIN 05 OCTOBER 1926 See abstract	28,29
A	US,A, 4,411,041 (BRAGA) 25 OCTOBER 1983 See abstract	28,29
A	US,A, 846,900 (BLOOM) 12 MARCH 1907 See abstract	28,29
A	US,A, 1,673,638 (PETERSON) 12 JUNE 1928 See abstract	28,29
A	US,A, RE 21,197 (HILL ET AL) 05 SEPTEMBER 1939 See abstract	28,29
	US,A, 2,216,333(WHITE) 01 OCTOBER 1990 See entire document	1,2,4,10,11,13,1 5,16,18,20,25- 29,33
	·	

Form PCT/ISA/210 (continuation of second sheet)(July 1992)*